


S Q U A R E deal

Feed-off-arm/cylinder/small cylinder bed interlock machine


Efficiency, Quality, User-friendly



JK-8740-460-02/D



Optional AW suction device makes seaming easy and stitch beautiful.




Large operation space design

The innovative frame design of the new patent provides a large operating space for sewing, which is more conducive to the sewing of large items and improves work efficiency and sewing effect.

Technical parameters

Model	Needles	Stitches	Stitch Width (mm)	Stitch Length (mm)	Differential Ratio	Presser Foot Height (mm)	Needle Distance (mm)	Speed (S.p.m)	Optional Device	Suction Device	Procedure
JK-8740-01	4	6	4.8 5.2	1.6-2.5	1:0.7-1:0.5	6-8	30	3200	D	AW1L S AW1S DS AW2L T1 AW2S T2	s
JK-8740-02	4	6	6.0 6.4	1.6-2.5	1:0.7-1:0.5	6-8	30	3200	UT		T1
JK-8740-02H	4	6	7.0 8.0	1.6-2.5	1:0.7-1:0.5	6-8	30	3200	UTL		

Name: Cylinder bed interlock Features: Efficiency, quality, user-friendly





1 Bottom threading improved

The elaborately improved way of the bottom threading makes the bottom thread more smooth, so that the thread ash will not run into the trimmer rack, so that the trimmer tangent is more stable, the part life is longer, precise fine tuning out the size of the trimmer.




2 Electromagnetic presser foot lifter

Electromagnetic presser foot lifter, quick and fast.

Technical parameters

Model	Stitch	Thread	Stitch Length	Stitch Width (mm)	presser Foot Height (mm)	Differential Ration	Speed (S.p.m)	Optional Device	Pulley
JK-8787-01G-356	3	5	1.4-4.5	5.6	7	0.8-1.4	4500		
JK-8787-01G-364	3	5	1.4-4.5	6.4	7	0.8-1.4	4500	D	
JK-8787-02B-356	3	5	1.4-4.5	5.6	7	0.8-1.4	4500	UT	PL
JK-8787-02B-364	3	5	1.4-4.5	6.4	7	0.8-1.4	4500	UT2	PR
JK-8787-35AC-356	3	5	1.4-4.5	5.6	7	0.8-1.4	4500	UTL	
JK-8787-35AC-364	3	5	1.4-4.5	6.4	7	0.8-1.4	4500		

Name: Small cylinder bed interlock Features: Efficiency, quality, user-friendly





1 Front type bottom line divider

The bottom thread cam is outside design, which can be easily clean thread from cam and adjusted easily. The adjustable bottom threading frame can adjust the bottom thread more precisely.



2 Mini direct drive servo motor

Direct drive externally connected with mini servo motor, hidden installation, responsive, silent, accurate positioning.

Technical parameters

Model	Stitch	Thread	Stitch Length	Stitch Width (mm)	Presser Foot Height (mm)	Differential Ration	Speed (S.p.m)	Optional Device
JK-8770-01G-356	3	5	1.4-4.5	5.6	7	0.8-1.4	4200	D UT
JK-8770-01G-364	3	5	1.4-4.5	6.4	7	0.8-1.4	4200	UT2 UTL

interlock sewing sample



1 suitable for pain seaming of knit and sportwear




3 Suitable for all kinds of casual wear, pleated cuffs, pleated hem



5 Suitable for elastic, swimsuit and rhythmic suit of various sizes


attachment					
D	direct drive				
UT	electronic auto-trimmer				
UT2	electronic wiper and looper trimmer				
UTL	pneumatic auto-trimmer				
PL	rear puller(gear)				
PR	rear puller (rubber)				
F	waistband attaching				
	Suction device				
AW1S	pneumatic small tube (25MM)				
AW1L	pneumatic big tube (32MM)				
AW2S	electronic small tube (25MM)				
AW2L	electronic big tube (32MM)				



2 Suitable for all kinds of sweatpants and trousers



4 Suitable for all kinds of sportswear, jackets, seam single side and double-side stitch



6 Suitable for all kinds of layering, men's underwear

	Sewing function
S	panty-hose
DS	diving suit
T1	Ribbon (lingerie)
T2	tape
Т3	Decorative sewing tape, suitable for 7mm ribbon
T4	Top and bottom tape seaming, suitable for 6-8mm ribbon
T5	tape seaming (adjustable press foot), suitable for 7-11mm ribbon
4L10	covered overlock stitch, the gap between the four rows of hook teeth is 1.0mm
4L15	covered overlock stitch, the gap between the four rows of hook teeth is 1.5mm
4L20	covered overlock stitch, the gap between the four rows of hook teeth is 2.0mm



Not sure which machine is best for you? Contact us for a free consult.We would love to help.

SQUARE DEAL SEWING MACHINES CC

190 Voortrekker Rd, Maitland, Cape Town, 7405 TEL: 021 510 5150

E-mail: info@sewingmachine.co.za www.sewingmachine.co.za